

TECHNICAL DATA

| | Q100 R | Q200 R | | Q100 R | Q200 R |
|----------------------|--------------------------|--------------------------|-------------------------------|--|--|
| Max. user weight: | 125 kg (19.5 st) | 136 kg (21 st) | Turning Circle: | 1500 - 1600 mm (59" - 63") | 1700 mm (67") |
| Seat width: | 380 - 540 mm (15" - 21") | 380 - 540 mm (15" - 21") | Max. safe slope: | 6° | 8° |
| Seat depth: | 405 - 505 mm (16" - 20") | 405 - 505 mm (16" - 20") | Max. kerb climbing: | 70 mm - 100 mm (with kerb climber) | 70 mm - 100 mm (with kerb climber) |
| Seat height: | 430 - 520 mm (17" - 20") | 430 - 520 mm (17" - 20") | Wheel options: | 12" drive wheels; 8" castor wheels | 14" / 12" drive wheels; 9" castor wheels |
| Backrest height: | 500 - 570 mm (20" - 22") | 500 - 570 mm (20" - 22") | Colour inlay choices | 4 colours: red, blue, green, black | 4 colours: red, blue, green, black |
| Backrest angle: | 0° to 12° (manual) | 0° to 12° (manual) | Max. range (ISO 7176-4) | 31 km (19 miles) | 31 km (19 miles) |
| Total width: | 540 mm (21") | 570 mm (22") | Wheelchair weight: | from 94 kg (including 55 Ah batteries) | from 98 kg (including 55 Ah batteries) |
| Total length: | 1010 mm (39.5") | 1070 mm (42") | Crash tested: | Yes - approved for forward facing transport in a vehicle (ISO 7176-19). Attachment: 4 chair fixing points with 2 double straps rear & 2 single straps front. No anchored belt restraints allowed. The ease of access and manoeuvrability in vehicles depends on the wheelchair size. | |
| Total Folded height: | 640 mm (25") | 680 mm (26.7") | | | |
| Fixed Angle Tilt | 0° - 6° | 0° - 6° | Transport without user: | Fix the wheelchair safe in the vehicle (e.g. car or plane) | |
| Max. speed: | 6 kph | 6 kph or 10 kph | Intended use and environment: | For people with limited mobility, indoor and outdoor use. Wheelchair type class B | |
| Battery size: | 40 / 50 / 55 Ah | 40 / 50 / 55 Ah | | | |
| Electronics: | VR2/R-Net | VR2/R-Net | | | |



Magbility